



Insulgrip®			
Weatherproof, Seal-Tite [®] , Triple Seal Boots			
Description	Catalog Number		
Seal-Tite [®] triple seal cover for plug when used on a cord set or when used with flush receptacles or connector bodies when used with flanged inlets. Black elastomer.	HBL6035		
Same as above except yellow.	HBL60CM35		
Seal-Tite triple seal cover for connector bodies, when used on interconnecting cord sets. Black elastomer.	HBL6036		
Same as above except yellow.	HBL60CM36		

Angle Adapter

Description	Catalog Number
Nylon, angle adapter for Insulgrip plugs and connectors, cord grip range	HBL45WAA
.350"-1.15" (8.9-29.2).	

PLUGOUT[®] Lockout Device

Description	Catalog Number
Lockout device for attachable 20 and 30A plugs, straight body or angle types, with or without weatherproof covers.	HLD
Lockout device for 20 and 30A, 4 and 5 wire angle plugs and watertight Safety-Shroud [®] Twist-Lock [®] plugs.	HLD2

Note: See page Z-3 for additional information on PLUGOUT Lockout devices. *When installed and used properly, with plug and connector body combinations.

Insulgrip[®] Plug and Connector Body Latching Kit

When you want to make doubly sure that plugs and connector bodies stay connected, the Hubbell latching kit provides both improved safety and security through a double locking feature that makes unintentional disconnection virtually impossible – even under high vibration situations. The plug and connector body lock once when first connected, then again when you push the special position locking slide into place.

Insulgrip[®] Latching Kit

Description	Catalog Number
For all 20 and 30A, 4 and 5 wire Twist-Lock Insulgrip plugs and connectors.	SK3

Twist-Lock[®] 3-Phase Circuit Tester

Description	Rating	20 Amp NEMA L21-20	30 Amp NEMA L21-30
3-Phase Circuit Tester	3Ø 120/208V AC Min. Voltage: 90V AC	HBL3PT2511	HBL3PT2811

Note: Testers in other NEMA configurations can be developed upon request.





HBL6035



HBL6036



HBL45WAA



HLD







HBL3PT2511

Dimensions in Inches (mm)