

Magnetic Contact

CATALOG

For All Your Security Needs

**Lifetime
Limited
Warranty**

Since
1971

Overhead Door Magnetic Contacts

SM-226LQ*
SM-226L-3Q

N.C.
NO/NC



- Gold and deactivated rhodium plating for longer life
- Switch contained in curved, low-profile, cast-aluminum housing, magnet in gray ABS case on L-bracket
- 24" (61cm) Wire leads enclosed in armored cable
- 2¾" (70mm) Gap



SM-226RQ*
SM-226R-3Q

N.C.
NO/NC



NEW

- Gold and deactivated rhodium plating for longer life
- Switch contained in curved, low-profile, cast-aluminum housing, magnet enclosed in round bracket
- 24" (61cm) Wire leads enclosed in armored cable
- 2¾" (70mm) Gap



SM-4201-LQ

N.C.

NEW

- Industrial, overhead door, track mount
- Rugged aluminum housing
- Adjustable to fit most door-channel widths
- 36" (91cm) Wire leads enclosed in armored cable
- 3" (76mm) Gap



SM-4601-LQ*
SM-4601-L3Q

N.C.
NO/NC



NEW

- Industrial, wide gap, surface mount
- Rugged aluminum housing
- Weatherproof and sealed for outdoor use
- 36" (91cm) Wire leads enclosed in armored cable
- 3" (76mm) Gap



Surface-Mount Magnetic Contacts

SM-200Q/W* *White, N.C.*

SM-200Q/BR* *Brown, N.C.*



- Standard surface mount
- Gold and deactivated rhodium plating for longer life
- Includes terminal cover
- ¾" (19mm) Gap



SM-431-TQ/W* *White, N.C.*

SM-431-TQ/B* *Brown, N.C.*



- Miniature surface mount
- Gold-plated terminals for longer life
- Screw mount using side flanges, or adhesive mount (mounting screws and double-sided tape included)
- 1" (25mm) Gap



SM-433-TQ/W* *White, N.C.*

SM-433-TQ/B* *Brown, N.C.*



- Surface-mount contact
- Gold-plated terminals for longer life
- Cover hides mounting screws, terminal block, and wires
- 1½" (31mm) Gap



SM-204Q/W* *White, N.C.*

SM-204Q/BR* *Brown, N.C.*



- Miniature "flange-type" surface mount
- Gold and deactivated rhodium plating for longer life
- Screw mount using flanges, or adhesive mount (double-sided tape included); flanges are removable
- 15" (38cm) Leads extend from center
- 1" (25mm) Gap



SM-216Q/GY* *Gray, N.C.*

SM-216Q/BR* *Brown, N.C.*



- Wide-gap surface mount for loose-fitting doors and windows
- Gold and deactivated rhodium plating for longer life
- Includes spacers
- 2¾" (70mm) Gap



SM-300Q/W* *White, N.O.*

SM-300Q/BR* *Brown, N.O.*



- Standard surface mount
- Gold and deactivated rhodium plating for longer life
- Includes terminal cover
- For N.O. circuits
- ¾" (19mm) Gap



SM-4003-TQ/W *White, N.C.*

- Miniature surface mount
- Gold-plated terminals for longer life
- Adhesive mount (double-sided tape included)
- 1" (25mm) Gap



NEW

SM-4004-TQ/W *White, N.C., terminals*

SM-4004-LQ/W *White, N.C., leads (18" / 46cm)*

NEW

- Miniature "capsule-type" surface mount
- Gold-plated terminals for longer life
- Adhesive mount (tape included)
- ¾" (19mm) Gap - SM-4004-LQ
- 1" (25mm) Gap - SM-4004-TQ



SM-205Q/W* *White, N.C.*

SM-205Q/BR* *Brown, N.C.*



- Miniature "flange-type" surface mount
- Gold and deactivated rhodium plating for longer life
- Screw-mount using flanges, or adhesive mount (double-sided tape included); flanges are removable
- 15" (38cm) Leads extend from side
- 1" (25mm) Gap



SM-217Q/W *White, N.C.*

- Miniature wide-gap surface mount for loose-fitting doors and windows
- Gold and deactivated rhodium plating for longer life
- Wide gap, yet contact is no longer than conventional surface type
- 2" (51mm) Gap



* Indicates UL-Listed products

Recessed-Mount Magnetic Contacts

SM-4102-TQ/W* *White, N.C.*



NEW

- 3/8" Press-fit mount
- Gold-plated terminals for longer life
- Switch and magnet have ribs for securing in holes
- 1" (25mm) Gap



SM-407-5TQ/W* *White, N.C.*



- 3/8" Press-fit mount with stubby magnet
- Gold-plated terminals for longer life
- Switch and magnet have ribs for securing in holes
- 3/4" (19mm) Gap



SM-207Q/W* *White, N.C.*



SM-207Q/BR* *Brown, N.C.*

- 3/8" Press-fit mount
- Gold and deactivated rhodium plating for longer life
- Unique glue/epoxy compound protects reed switch
- Switch and magnet have ribs for securing in holes
- 15" (38cm) Wire leads
- 1" (25mm) Gap



SM-207-5Q/W *White, N.C.*

SM-207-5Q/BR *Brown, N.C.*

- Similar to SM-207Q but with stubby 3/4" (19mm) magnet and switch
- 3/8" (10mm) Gap



SM-206Q/W* *White, N.C.*



SM-206Q/BR* *Brown, N.C.*

- 1/4" Press-fit mount
- Gold and deactivated rhodium plating for longer life
- Unique glue/epoxy compound protects reed switch
- 15" (38cm) Wire leads
- 1" (25mm) Gap



SM-207-5LQ/W* *White, N.C.*



SM-207-5LQ/BR* *Brown, N.C.*

- Similar to SM-207Q but with stubby 3/4" (19mm) switch
- 1" (25mm) Gap



SM-4103-TQ/W *White, N.C.*

NEW

- 3/8" Press-fit mount with stubby 1" (25mm) switch
- Gold-plated terminals for longer life
- Rare-earth magnet with nickel plating to protect against chipping and corrosion
- Switch has ribs for securing in hole
- 1/2" (13mm) Gap



SM-4103-LQ/W* *White, N.C.*



NEW

- Similar to SM-4103-TQ/W but with 18" (46cm) wire leads



SM-4104-TQ/W* *White, N.C.*



NEW

- 3/4" (19mm) Steel-door recessed mount
- Gold-plated terminals for longer life
- Strong one-piece construction
- Switch and magnet have ribs for securing in hole
- 1" (25mm) Gap (on steel)



SM-4105-LQ/W* *White, N.C.*



NEW

- Similar to SM-4104-TQ/W but with 18" (46cm) wire leads



* Indicates UL-Listed products

Plunger-Type Magnetic Switches

SM-4301-TQ/W* *White, N.C.*

- Pushbutton
- Magnet and reed switch contained in housing
- Spacer and screws included
- Quick-connect terminals
- Roller travel is 1/4" (6mm)



NEW



SM-4303-TQ/W* *White, N.C.*

- Quick-connect terminals
- 360° Rollerball
- Magnet and reed switch contained in housing
- Spacer and screws included
- Roller travel is 1/4" (6mm)



NEW



SM-4302-LQ/W* *White, N.C.*

- 18" (46mm) Wire leads
- 360° Rollerball
- Magnet and reed switch contained in housing
- Spacer and screws included
- Roller travel is 1/4" (6mm)



NEW



Accessories

SM-831

*Alnico 5 magnet,
1 1/4" (32mm) length x
1/4" (6mm) diameter*



SM-841

*Alnico 5 magnet,
1 5/8" (41mm) length x
3/8" (10mm) diameter*



SM-851

*Aluminum "Z" bracket
for SM-216Q/SM-226LQ*



SM-852LQ

*Aluminum "L" bracket
for SM-216Q/SM-226LQ*



* Indicates UL-Listed products

WARRANTY: This SECO-LARM product is warranted against defects in material and workmanship while used in normal service for the lifetime of the product. SECO-LARM's obligation is limited to the repair or replacement of any defective part if the unit is returned, transportation prepaid, to SECO-LARM. This Warranty is void if damage is caused by or attributed to acts of God, physical or electrical misuse or abuse, neglect, repair or alteration, improper or abnormal usage, or faulty installation, or if for any other reason SECO-LARM determines that such equipment is not operating properly as a result of causes other than defects in material and workmanship. The sole obligation of SECO LARM and the purchaser's exclusive remedy, shall be limited to the replacement or repair only, at SECO-LARM's option. In no event shall SECO-LARM be liable for any special, collateral, incidental, or consequential personal or property damage of any kind to the purchaser or anyone else.

NOTICE: The information and specifications printed in this catalog are current at the time of publication. However, the SECO-LARM policy is one of continual development and improvement. For this reason, SECO-LARM reserves the right to change specifications without notice. SECO-LARM is also not responsible for misprints or typographical errors.

Copyright © 2015 SECO-LARM U.S.A., Inc. All rights reserved. This material may not be reproduced or copied, in whole or in part, without the written permission of SECO-LARM.

SECO-LARM® U.S.A., Inc.

16842 Millikan Avenue, Irvine, CA 92606

Phone: (949) 261-2999 | (800) 662-0800

Website: www.seco-larm.com

Email: sales@seco-larm.com



MagneticContactCatalog_150120.
indd