





1

2

3

4

5



PCB LAYOUT - COMPONENT VIEW

TECHNICAL CHARACTERISTICS

MATERIAL

INSULATOR MATERIAL: PA 9T
FLAMMABILITY RATING UL94-V0
COLOUR: BLACK
CONTACT MATERIAL: COPPER ALLOY
CONTACT TYPE: STAMPED
CONTACT PLATING: SELECTIVE GOLD
SHIELDING: BRONZE NI PLATED
QUALITY CLASS: 500 MATING CYCLES

ENVIRONMENTAL

OPERATING TEMPERATURE: -40 °C UP TO 85 °C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL

CURRENT RATING: 1.5 A
WORKING VOLTAGE: 120 VAC
INSULATION RESISTANCE: >500 MOHM
DIELECTRIC WITHSTANDING VOLTAGE: 1 000 VAC/MN
CONTACT RESISTANCE: 20 mOHM MAX

STANDARD

 CERTIFIED: E324776

SOLDERING


REFLOW PROCESS - 1TIME
TEMPERATURE PROFILE IDENTICAL TO JEDEC PROFILE

PACKAGING

TRAY

RoHS Compliant

PROJECTION:



GENERAL TOLERANCE

.X = ± 0.2

.XX = ± 0.15



APPROVAL: RJ

UNIT: MM

SCALE:

SHEET: 1/2


DRAW: JOE

DESCRIPTION: HORIZONTAL SHIELDED SMT WITH LED AND EMI PANEL
FINGER 8P8C MODULAR JACK TAB UP

WERI PART NO: 634 008 137 521

SIZE

A4



RoHS Compliant				PROJECTION:	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15				
G									
F									
E									
D									
C				APPROVAL: RJ	UNIT: MM	DESCRIPTION: HORIZONTAL SHIELDED SMT WITH LED AND EMI PANEL FINGER 8P8C MODULAR JACK TAB UP			SIZE A4
B					SCALE:				
A					SHEET: 2/2	WERI PART NO: 634 008 137 521_TPK			
REV	DATE	FILE	BY		DRAW: PEARL				