



## MECHANICAL DETAILS

<b>Shell Style Model</b>	PCA* : Free receptacle cable collet
<b>Keying</b>	Hermaphroditic keying (&quot;half moon&quot; insert), plug has male pin 1
<b>Housing Material</b>	Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces
<b>Cable Fixing</b>	3.8 - 4.4 mm

**Variant 2** :

	A	C	L	S2
Mm.	8.9	4.2	33.5	6.5
In.	0.35	0.17	1.32	0.26



## PERFORMANCE DETAIL

<b>Insert</b>	0S.302 : 2 Low Voltage
<b>Insulator</b>	L: PEEK
<b>Specifications</b>	
<b>Contact Type:</b>	Solder
<b>Max. Matings:</b>	5000
<b>Contact Dia.:</b>	0.9 mm (0.0354in)
<b>Bucket Dia.:</b>	0.8 mm (0.031in)
<b>Max. Solid</b>	0.34 mm <sup>2</sup> (AWG 22)
<b>R (max):</b>	4.8 mOhm

## OTHER CHARACTERISTICS







<b>Endurance (Shell)</b>	Endurance (Shell):
<b>Temp (min)</b>	-55°C
<b>Temp (max)</b>	+250°C
<b>Humidity (max):</b>	<=95% [at 60 deg C /140 F]
<b>Vibration:</b>	15 g [10 Hz - 2000 Hz]
<b>Shock Resistance:</b>	100 g [ 6 ms]
<b>Salt Spray</b>	>144 hr
<b>Climatical</b>	50/175/21
<b>Shielding (min):</b>	75 dB (10 MHz)
<b>Shielding (min):</b>	40 dB (1 GHz)
<b>IP Rating</b>	50



## Available Download

 [unipole\\_multipole.pdf](#)

## Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)