



For Information Only
won't be replaced when changed

M12 A-coded 4-poles, female angled connector

M12 A-coded 4-poles, male straight connector

Loading-Plan:

- 1 brown
- 2 white
- 3 blue
- 4 black

- Protection level: IP67
- Temperature range: -25°C ... +80°C

length in "1m" step	40	XXX=400
	39	XXX=390
	12	XXX=120
	11	XXX=110
length in "0,1m" step	10	XXX=100
	9,9	XXX=099
	9,8	XXX=098
	0,4	XXX=004
	0,3	XXX=003
	0,2	XXX=002
	0,1	XXX=001
Step	a [m]	XXX

4,0 to 40	+1%
0,1 to 3,9	+0,04
a [m]	Tolerance

Part no.	213484874XXX
----------	--------------

Type of cable	XX
PVC grey, 4x0,34mm ²	XX=84
PP black, 4x0,34mm ²	XX=91

All rights reserved Department EC PD - RO HARTING Electronics GmbH D-32339 Espelkamp	All Dimensions in mm Original Size DIN A3	Scale 2:1 Free size tol.	Ref. Sub.
	Created by TOMUTA Title M12 A-coded Cable Assembly Type TB	Inspected by Standardisation Number 213484874XXXX	Date 2014-05-23 State Checked Out