




FACE VIEW-FEMALE INSERT
A-CODE



- 1 BROWN
- 2 WHITE
- 3 BLUE
- 4 BLACK



W04001A09MXXX

CABLE TYPE
4x22AWG
PVC YELLOW

CABLE LENGTH
003----0.3 METER
010----1 METER
100----10 METER

SPECIFICATIONS:

ULTRA LOCK FEMALE:
COUPLING NUT MATERIAL: NICKEL PLATED BRASS
CONTACT MATERIAL: GOLD/NICKEL OVER COPPER ALLOY
INSERT MATERIAL: BLACK PUR
O-RING: GREEN FPM
OVERMOLD: YELLOW PUR

CABLE: #22/4 YELLOW PVC JACKET, 105°C 300V
CABLE MARKING: RU AWM 2661 22 AWG/4C 105°C 300V (UL FILE NUMBER) CSA
AWM I/II A/B 80°C 300V FT1
ASSEMBLY RATINGS: 250V Max., 4A Max.
PACKAGING: CABLE ASSEMBLIES ARE BAGGED SEPARATELY IN POLY BAGS
WITH BAR CODE LABEL ATTACHED TO OUTSIDE OF BAG

CORRECTED WIRE STRIP EC NO: IPG2014-1957 DRWN: RSTONE CHKD: B ARDEN APPR: BWOODMAN 5/12/14	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ∇=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
				mm	INCH	IN/MM		NTS	INCH			
			4 PLACES	±---	±---	DRAWN BY	DATE	TITLE				
			3 PLACES	±---	±.005	TWOLDEG	2009/07/06	MICRO CHANGE ULTRA LOCK 4-POLE FEMALE 90 DEGREE #22/4 PVC CABLE				
	2 PLACES	±0.13	±.010	CHECKED BY	DATE	MATERIAL NO.						
	1 PLACE	±0.25	±.020	BWOODMAN	2009/07/06	DOCUMENT NO.						
	ANGULAR ±1/2°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		APPROVED BY		DATE	MATERIAL NO.		SHEET NO.		
C	B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
						SD-120079-011		1 OF 1				

F

E

D

C

B

A

F

E

D

C

B

A

10

9

8

7

6

5

4

3

2

1

10

9

8

7

6

5

4

3

2

1