


A B C D E



| No. of Pin | Part. No. | A | B |
|------------|--------------------|------|------|
| 4 | DF11-4DP-2DSA(01) | 6.0 | 2.0 |
| 6 | DF11-6DP-2DSA(01) | 8.0 | 4.0 |
| 8 | DF11-8DP-2DSA(01) | 10.0 | 6.0 |
| 10 | DF11-10DP-2DSA(01) | 12.0 | 8.0 |
| 12 | DF11-12DP-2DSA(01) | 14.0 | 10.0 |
| 14 | DF11-14DP-2DSA(01) | 16.0 | 12.0 |
| 16 | DF11-16DP-2DSA(01) | 18.0 | 14.0 |
| 18 | DF11-18DP-2DSA(01) | 20.0 | 16.0 |
| 20 | DF11-20DP-2DSA(01) | 22.0 | 18.0 |
| 22 | DF11-22DP-2DSA(01) | 24.0 | 20.0 |
| 24 | DF11-24DP-2DSA(01) | 26.0 | 22.0 |
| 26 | DF11-26DP-2DSA(01) | 28.0 | 24.0 |
| 28 | DF11-28DP-2DSA(01) | 30.0 | 26.0 |
| 30 | DF11-30DP-2DSA(01) | 32.0 | 28.0 |
| 32 | DF11-32DP-2DSA(01) | 34.0 | 30.0 |

Notes: The minimum ordering quantity for header is one package(containing 100 pieces).
 2: Insulator : Nylon resin ,Black
 Contact Material: Brass
 Contact Plating : 0.2 μm gold plating

| REVISIONS | BY | CHKD | DATE | REVISIONS | BY | CHKD | DATE |
|-----------|----|------|------|-----------|----|------|------|
| Δ | | | | Δ | | | |
| Δ | | | | Δ | | | |
| Δ | | | | Δ | | | |

| | | | | | |
|-------------|----------------|-----------------|-----------------------------|----------|--------------------------------|
| No. | MATERIAL | FINISH, REMARKS | No. | MATERIAL | FINISH, REMARKS |
| APPROVED | 14 Yamazaki | 20.8.29 | GENERAL DIMENSION TOLERANCE | HRS | HIROSE ELECTRIC CO., LTD. |
| REVIEWED | | | 6 of less ±0.3 | | ISSUED BY |
| CHECKED | | | over 6 to 18 ±0.5 | | |
| DESIGNED | J.Om A | 90.8.29 | over 18 to 50 ±0.7 | | |
| DRAWN | J.Om A | 90.8.29 | over 50 to 125 ±1 | | |
| DRAWING No. | EDC3-162393-01 | | over 125 to 250 ±1.3 | | |
| | | | ANGULAR | | |
| | | | UNITS | SCALE | CODE NO. |
| | | | mm | 5:1 | DF11- X DP-2DSA(01) |