



ITEM-NO. (ITEM-NO.)	236-746
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	5 - 6
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	24
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	1
Height (Height / mm)	13
Width (Width / mm)	5
Depth (Depth / mm)	14
No. of connection Points (No. of connection Points)	1
No. of potentials (No. of potentials)	1
COLOR (COLOR)	orange
Dimensions (Dimensions)	1,1 + 0,1 mm
RGB (RGB)	1,0.58,0.16,0