


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. ** (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT1M-76	.13 (3.3)	.87 (22)	.043 (1.1)	.098 (2.5)	.159 (4.0)	.186 (4.7)	.188 (4.8)	4.0 (102)	18 (80)	MINIATURE	CURVED	.09 (42)
PLT2I-76	.13 (3.3)	2.00 (51)	.045 (1.1)	.135 (3.4)	.200 (5.1)	.180 (4.6)	.260 (6.6)	8.0 (203)	30 (133)	INTERMEDIATE	CURVED	.28 (127)
PLT2S-76	.13 (3.3)	1.88 (48)	.055 (1.4)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	7.40 (188)	50 (222)	STANDARD	CURVED	.47 (213)
PLT3S-76	.13 (3.3)	3.00 (76)	.059 (1.5)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	11.60 (295)	50 (222)	STANDARD	CURVED	.78 (352)
PLT4S-76	.13 (3.3)	4.00 (102)	.059 (1.5)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	14.60 (371)	50 (222)	STANDARD	CURVED	.89 (404)
PLT3H-76	.25 (6.4)	3.00 (76)	.075 (1.9)	.300 (7.6)	.370 (9.4)	.360 (9.1)	.480 (12.2)	11.50 (292)	120 (534)	HEAVY	STRAIGHT	1.5 (687)
PLT4H-76	.25 (6.4)	4.00 (102)	.075 (1.9)	.300 (7.6)	.370 (9.4)	.360 (9.1)	.480 (12.2)	14.60 (371)	120 (534)	HEAVY	STRAIGHT	1.83 (830)

NOTES:

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

- *1) *SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.
- 2) MATERIAL HAS A UL RELATIVE THERMAL INDEX RATING OF 338°F (170°C).
- 3) MATERIAL FLAMMABILITY RATING: UL94V-0.
- 4) EXCELLENT RESISTANCE TO MOST CHEMICALS.
- **5) MINIMUM LOOP TENSILE RATING AT 73°F (23°C).
- 6) MEETS REQUIREMENTS OF IEEE 383 PANDUIT QUALIFICATION TEST REPORT NO. 42481.

CAGE CODE
06383

TITLE PAN-TY CABLE TIES - PLT ELEVATED TEMPERATURE SERIES		CUSTOMER DRAWING	
ITEM REVISION NAME W10001BK/27		PANDUIT	
DATASET FILE NAME W10001BK/27-SS-4994_REV27			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .xxxx .xxx ± .020 (.51) .xx ± .02 (.5) ANGLES ± .xxxx		MATERIAL: TEFZEL FLUOROPOLYMER COLOR: AQUA BLUE REG. T.M. OF DUPONT CO.	
THIRD ANGLE PROJECTION		DRAWING NUMBER: SS-4994	
DRAWN BY CEW	DATE 3-8-85	CHK HVP	SCALE NONE
SHT 1 OF 1		SIZE A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
27	10/10/15	BWG	DJSL	JADE	REVISED NOTE 1 AND PLT2I MIN. TENSILE WAS 25 (111). UPDATED TITLE BORDER.	SS-4994/27