



1) Einlotstifte passend für Lochungen  
 Ø1 ±0,1 nach IEC 60326-3  
*Solder pins for PCB connections  
 Ø1 ±0,1 as per IEC 60326-3*  
 A souder pour des trous de Ø1 ±0,1  
 selon IEC 60326-3

		 All Dimensions in mm Original Size DIN A 4		Techn. Character.			Nicht tolerierte Masse/ Free size tolerances														
A	09185607322	3	4,5	<table border="1"> <tr> <td>Detail.</td> <td>01-FEB-00</td> <td>JB</td> </tr> <tr> <td>Insp.</td> <td>01-FEB-00</td> <td>JMV</td> </tr> <tr> <td>Stand.</td> <td></td> <td></td> </tr> </table>	Detail.	01-FEB-00	JB	Insp.	01-FEB-00	JMV	Stand.			<table border="1"> <tr> <td colspan="2">Massstab/ Scale</td> </tr> <tr> <td colspan="2" style="text-align: center; font-size: 24px;">1,5:1</td> </tr> </table>	Massstab/ Scale		1,5:1		SEK 18 Male connector 60 poles low profile with straight pins		
	Detail.	01-FEB-00	JB																		
	Insp.	01-FEB-00	JMV																		
	Stand.																				
Massstab/ Scale																					
1,5:1																					
09185606322	2	4,5																			
09185607324	3	2,9																			
09185606324	2	2,9																			
Bestell-Nr. Part-No. Reference	Anforderungsstufe performance level Niveau de qualite	a	<table border="1"> <tr> <td>26570</td> <td>01-FEB-00</td> <td>JB</td> </tr> <tr> <td>Mod.</td> <td>Dat.</td> <td>Name</td> </tr> </table>	26570	01-FEB-00	JB	Mod.	Dat.	Name	HARTING EURL F-95972 Paris 		<table border="1"> <tr> <td>TB</td> <td>0918560x32x</td> </tr> <tr> <td>Sub.</td> <td></td> </tr> </table>		TB	0918560x32x	Sub.		<table border="1"> <tr> <td>Blatt/ page</td> </tr> <tr> <td style="text-align: center;">1 / 2</td> </tr> </table>	Blatt/ page	1 / 2	
26570	01-FEB-00	JB																			
Mod.	Dat.	Name																			
TB	0918560x32x																				
Sub.																					
Blatt/ page																					
1 / 2																					