
PRODUCT DATA DRAWING



MATERIAL:

CONNECTORS:	SYNAPSE MALE		
	2.92mm MALE		


CABLE:	FLEXIBLE Ø.047 CABLE

SHRINK TUBING: M23053/5

PERFORMANCE:

IMPEDANCE:	50 OHMS	
FREQ. RANGE:	DC TO 40.0 GHz	

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: +1/64 ANGULAR: X° +1°0'	UNLESS C
FINISH:	SEE NOTES	X°X' ±15' DECIMAL: .X ±.030 .XX ±.010	1) ALL DIMENSIONS 2) ALL DIMENSIONS 3) BREAK CORNERS 4) CHAM, 1ST & LAS
SURFACE ARE	^{EA:} N/A	.XXX ±.005	5) SURFACE ROUGH 6) DIA.'S ON COMMC WITHIN .005 T.I.R. 7) REMOVE ALL BUR
	PROPRIETARY	PER ASME Y14.5M - 1994	I) ILLIIO VE MEE BOIN
THE INFORMAT	ION CONTAINED IN THIS DRAWING	THIRD ANGLE PROJECTION	DRAWN:
ANY REPRODU	CTION IN PART OR AS A WHOLE WRITTEN PERMISSION OF		CHECKED
	E, INC IS PROHIBITED.		APPROVE



OTHERWISE SPECIFIED S ARE IN INCHES [MILLIMETERS] S ARE AFTER PLATING.				
TS & EDGES .005 R. MAX. ST THREADS SHNESS 63∗MIL-STD-10. ION CENTERS TO BE CONCENTRIC R. JRRS	TITLE: SYNAPSE MALE TO 2.92mm MALE FOR FLEXIBLE Ø.047		Ø.047	
KRR 08/06/20		(CABLE ASSEMBI	LY
D: BNK 08/06/20	SIZE B	DWG. NO.	7080-0	0840
ED: BNK 08/06/20	S	CALE: 4:1		SHEET 1 OF 1