



**NOTES:**

1. METAL SHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
2. INSULATORS: PBT GF UL 94 V-0; GREEN
3. SIGNAL CONTACTS: COPPER ALLOY  
PLATING: 30µm HARD GOLD over min. 50µm NICKEL  
SOLDER CUP ACCEPTS CABLE AWG 20
4. NO CONTACTS ON POS. A1 + A2
5. CONNECTOR IS PART MARKED: 3007W2SCM99A10X CONEC ABC

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH  DO NOT ALTER CAD DRAWING BY HAND					tolerance		scale: 2:1 (5:1)
					date	name	material: SEE NOTES
					drawn	07.05.02 Parei	title: <b>D-SUB COMBINATION FEMALE 7W2S SOLDER CUP</b>
					appd.	07.05.02 Mickenbecker	
					norm		
					d-old		dwg no:
1 x b	Ä5839	01.10.2015	K.H.			13K1A563	DIN-A3
a	Original					sh: 1	
rev.	description	date	name			part no: 3007W2SCM99A10X	