



Note:

ROHS 2.0 & REACH Compliant

2. The out jacket is conform to IEC60332-1, EN60754-2, EN61034-2

3. Min. Bending Radius: Static: 30mm, Dynamic: 60mm

Test:

Grade Designation: Each to Reference

Type	Single-mode
Insertion Loss	≤0.3dB
Return Loss	≥60dB
Test Wavelength	1310nm

MATERIAL LIST:

⑨	Fiber Optical Cable Duplex $\phi$ 3.0 OS2(G657.A2) 9/125um white LSZH Armored (only Stainless steel spiral pipe, no Stainless Steel braiding)	L	
⑧	Black Heat shrink tubing	2	
⑦	Ring (1)	2	
⑥	Ring (2)	2	
⑤	LC White Boot	4	
④	LC Green Clip	2	
③	LC 3.0 SM Green Duplex Connector	4	
②	LC/APC SM Ferrule $\phi$ 125-126um	4	
①	LC White Dust cap	4	
NO	SPECIFICATION STANDARD	QT'Y	REMARK

21.15.8630	Roline FO Jumper Arm. Cbl, OS2 DPX, LSOH, APC, LC-LC, 1m
21.15.8631	Roline FO Jumper Arm. Cbl, OS2 DPX, LSOH, APC, LC-LC, 2m
21.15.8632	Roline FO Jumper Arm. Cbl, OS2 DPX, LSOH, APC, LC-LC, 3m
21.15.8633	Roline FO Jumper Arm. Cbl, OS2 DPX, LSOH, APC, LC-LC, 5m
21.15.8634	Roline FO Jumper Arm. Cbl, OS2 DPX, LSOH, APC, LC-LC, 7m
21.15.8635	Roline FO Jumper Arm. Cbl, OS2 DPX, LSOH, APC, LC-LC, 10m
21.15.8636	Roline FO Jumper Arm. Cbl, OS2 DPX, LSOH, APC, LC-LC, 15m
21.15.8637	Roline FO Jumper Arm. Cbl, OS2 DPX, LSOH, APC, LC-LC, 20m
ITEM NO.	Product description

**SECOMP**

		NEW	2022-02-07	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.