



AS SHOWN  
Wie gezeigt: 2356256-1



DIMENSION AND TOLERANCES ACCORDING TO:  
Bemaßungen und Toleranzen gemäß:

DIN 3302-1 M1  
DIN 3302-1 M2

DIN EN ISO 8015 (AD) - DIN EN ISO 291  
DIN EN ISO 14405


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	26JUL2019	NS	KS
	A1	Appl. and Prod. Spec. added	27JUL2020	KS	JB

NOTES  
Bemerkungen

- TE ORDER NUMBER  
TE Bestell-Nummer
- REVISION  
Revision
- MOLD CAVITY MARKING  
Nestmarkierung

SCALE 4:1



THIS DRAWING IS A CONTROLLED DOCUMENT.  
DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±
	1 PLC ±
	2 PLC ±
	3 PLC ±
	4 PLC ±
	ANGLES ±
	FINISH SEE TABLE siehe Tabelle

DWN	26JUL2019
CHK	Nandesh Sali
APVD	29JUL2019
APVD	K. Schang
APVD	J. Barth
PRODUCT SPEC	108-94752 (A1)
APPLICATION SPEC	114-94625 (A1)
WEIGHT	SEE TABLE
CUSTOMER DRAWING	

TE Connectivity		NAME			
		BLIND PLUG FOR HDSCnet+			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
A3	00779	©=2356256	-		
SCALE		SHEET	OF	REV	
5:1		1	1	A1	

TE ORDER-NO. TE Bestell-Nr.	REV.	QTY Anzahl	MATERIAL	COLOUR Farbe	WEIGHT (g)	DESCRIPTION Beschreibung	ITEM
2356256-1	A	1	SILICON RUBBER	GREEN Grün	0.45	BLIND PLUG FOR HDSCnet+	1