



### Liquid-Tight, Strain Relief Cordgrips

- Black nylon, liquid-tight cordgrip
- Used where cable is entering or leaving an enclosure
- Accepts a wide range of cable diameters due to large opening and highly flexible strain relief elements, together with a TPE sealing ring
- The strain relief elements tighten in a circular sequence on the sealing ring to give outstanding strain relief without twisting or damaging the cable
- Use the cordgrip with the smallest maximum diameter that will fit your application (see table below)
- Nylon locknut included (as shown)
- Suitable for NEMA type 4 applications - Protection to IP68
- UL94-V2 flammability rating
- UL, CSA & VDE listed

Part Number	Use With Wire Diameter		Mounting Hole Diameter	
	Inch	mm	Inch	mm
<b>1427CG7</b>	0.099-0.256	2.5-6.5	0.492	12.5
<b>1427CG9</b>	0.138-0.315	3.5-8	0.599	15.2
<b>1427CG13</b>	0.236-0.472	6-12	0.804	20.4
<b>1427CG16</b>	0.354-0.551	9-14	0.886	22.5
<b>1427CG21</b>	0.512-0.709	13-18	1.115	28.3