

AT6402

- Very high tack
- Very good adhesion
- Easy tear
- Conformable to awkward shapes

Applications

- Fitting of carpet & other floor coverings

| | |
|---------------|----------------|
| Thickness | 0.25mm |
| Breaking Load | 22 N/cm |
| Elongation | 4% |
| Faced Side | 20 N/cm |
| Unfaced Side | 20 N/cm |
| Service Temp | -10°C to +50°C |

