



MINWA

(CHINA)

ELECTRONICS

M.A.T.002E1
MANUFACTURE CO.,LTD

Model: MB090A050U/D

TECHNICAL DATA (技术数据)

page:2

Standard Specification: (测试标准)EN61558-1:1998**Client Number** (客户名称): -----**Sample No** (样板编号): -----**Model Number** (型号): MB090A050U/E**Type** (类型): Single-Voltage AC/AC Adaptor:**1.Electrical Data** (电子数据)

Input 输入	Input Voltage/Frequency (输入电压/频率)	230V~50Hz
	Input Power (输入功率)	8W
Output 输出	Rated Output Voltage (额定输出电压)	9V
	Rated Output Load Current (额定输出电流)	500mA
	Rated Output Power (额定输出功率)	4.5VA
Resistance 阻抗	Insulation Resistance (绝缘阻抗)	100MΩ (measured with 500 DC Voltage)
Protection (保护)	Thermal Protection (热敏保护)	Thermal fuse:125°C/2A
	Withstand Voltage (Hi-Pot) (高压)	AC 3750V 50Hz for 1minute or AC 4000V 2seconds

2.Mechanical Data (机械数据)

Supply Connection Type (输入插)	UK
Primary Turns & Wire Gauge (初级圈数和线径)	3220T/0.09(mm)
Secondary Turns & Wire Gauge (次级圈数和线径)	224T/0.37(mm)
Core Size (铁芯尺寸)	41x 16 (mm)
Output Plug Dimensions (输出插尺寸)	5.5x2.1x12mm
Polarity (极性)	-----
Unit Weight (净重)	240g
Dimensions (外形尺寸)	67 x 50 x 72(mm)

3. Output Voltage (输出电压)Test by: (测试人) 刘建国 Checked by: (审核人) 廖东风 Date: (日期) 2010-11-12.



MINWA

(CHINA)

ELECTRONICS

MANUFACTURE CO.,LTD

Model: MB090A050U/D

TECHNICAL DATA (技术数据)

page:2

Sample 样板	Unload output current (空载输出电流) ——0—— mA		Full-load output current (满载输出电流) ——500—— mA	
	Output Voltage (输出电压)	Ripple Voltage (纹波电压)	Output Voltage (输出电压)	Voltage Range (电压范围)
1	15.33V	-----	12.02V	11.4-12.6V

Test by: (测试人) 刘建国 Checked by: (审核人) 廖东风 Date: (日期) 2010-11-12.