

8728 Multi-Conductor - Special Audio, Communication and Instrumentation Cable



For more Information
please call

1-800-Belden1



Description:

22 AWG stranded (7x30) TC conductors, polypropylene insulation, cabled in pairs, overall Beldfoil® shield (100% coverage), 24 AWG stranded TC drain wires, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
2	22	7x30	TC - Tinned Copper	0.762

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)	Dia. (mm)
PP - Polypropylene	0.254	1.27

Inner Shield

Inner Shield Material:

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Layer 1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
Layer 2		Tape	Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Stranding: Stranded

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	Stranded	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.7112

Overall Cabling

Overall Nominal Diameter: 5.461 mm

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red
2	White & Green

Pair Lay Length & Direction:

Lay Length (mm)	Twists/ft. (twist/m)

8728 Multi-Conductor - Special Audio, Communication and Instrumentation Cable

31.749875	31.498
-----------	--------

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
UL Temperature Rating:	80°C (UL AWM Style 2717)
Bulk Cable Weight:	41.670 Kg/Km
Max. Recommended Pulling Tension:	161.914 N
Min. Bend Radius (Install)/Minor Axis:	31.750 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
NEC Articles:	800
CEC/C(UL) Specification:	CM
AWM Specification:	UL Style 2717 (300 V 80°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
50

Nom. Inductance:

Inductance (µH/m)
0.59058

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
114.835

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
203.422

Nominal Velocity of Propagation:

VP (%)
66

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
55.777

METRIC MEASUREMENT VERSION

8728 Multi-Conductor - Special Audio, Communication and Instrumentation Cable

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 54.465 Ohm/km

Max. Operating Voltage - UL:

Voltage
300 V RMS (UL AWM Style 2717)

Max. Recommended Current:

Current
2.3 Amps per conductor @ 25°C

Notes (Overall)

Notes: Each pair Beldfoil® shielded with individual drain wire plus a polyester film over each shield.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8728 060U1000	305 MT	13.608 KG	CHROME		2 #22 SHPR PP PVC
8728 060U500	152 MT	7.031 KG	CHROME		2#22 SHPR PP PVC
8728 0601000	305 MT	14.061 KG	CHROME	C	2 #22 SHPR PP PVC
8728 060500	152 MT	7.031 KG	CHROME	C	2#22 SHPR PP PVC

Notes:
C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-16-2008

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.