


Prototyping Board



RE220-HP



- SRBP-paper FR2 1.5 mm single-sided 35 µm CU
- organic soldering protection (OSP)
- 37 x 58 single-hole conductor 2.2 mm Ø
- hole spacing 2,54 x 2,54 mm
- hole dia 1.0 mm
- connector 31-channel DIN 41617
- size 100 x 160 mm