


## Prototyping Board



### RE524-HP



- SRBP-paper FR2 1.5 mm single-sided 35 µm CU
- organic soldering protection (OSP)
- 36 continuous strips with 61 borings
- hole spacing 2.54 x 2.54 mm
- hole dia 1.0 mm
- connector 32-channel DIN 41612
- grid 5.08 mm type D
- size 100 x 160 mm