


Prototyping Board for D-Sub connector DIN 41652



RE224-HP



- SRBP-paper FR2 1.50 mm single-sided 35 µm CU
- organic soldering protection (OSP)
- connector D-Sub DIN 41652
- 2 x 9- channel and 2 x 15- channel
- 48 x 35 single hole conductor 2.10 mm Ø
- hole spacing 2.54 x 2.54 mm
- hole dia 1.0 mm
- 2 potential strips
- size 100 x 160 mm