


Prototyping Board



RE526-HP



- SRBP-paper FR2 1.50 mm single-sided 35 µm CU
- organic soldering protection (OSP)
- 36 continuous strips with 56 holes
- hole spacing 2.54 x 2.54 mm
- hole dia 1.00 mm
- additional print at the component side
- Connector DIN 41612 Typ H 15-channel
- hole spacing 5.08 mm
- size 100 x 160 mm