

## Prototyping Board



### RE527-HP



- SRBP-paper FR2 1.50 mm single-sided 35 µm CU
- organic soldering protection (OSP)
- additional print at the component side
- 38 continuous strips with 57 holes
- hole spacing 2.54 x 2.54 mm
- hole dia 1.00 mm
- connector:
  - 32-channel DIN 41612 type C a 2.54 mm
  - 32-channel DIN 41612 type D a+c 5.08 mm
- size 100 x 160 mm