

## Strada-D Strada-DW-N83 series



<b>Ordering number</b>	<b>C11242</b>		
<b>Description</b>	<b>C11242-Strada-DW-MX6</b>		
Family	Strada-D	FWHM	90+144 degrees
Type	Lens	Efficiency	-
LED	MX-6	cd/lm	-
Color	Transparent	Gerber File	Available
Diameter	19.6 x 15.7 mm		
Height	12 mm		
Style	Rectangular		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		



<b>Ordering number</b>	<b>CA11243</b>		
<b>Description</b>	<b>CA11243-Strada-DW-MX6-tape</b>		
Family	Strada-D	FWHM	90+144 degrees
Type	Lens	Efficiency	-
LED	MX-6	cd/lm	-
Color	Transparent	Gerber File	Available
Diameter	19.6 x 15.7 mm		
Height	12 mm		
Style	Rectangular		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		