

Main

Range of product	GV2ME GV2P TeSys D TeSys U
Device short name	GV1
Product or component type	Power connectors
Accessory / separate part type	Terminal block
Poles description	3P
Product compatibility	GV2

Complementary

[Ie] rated operational current	63 A
IP degree of protection	IP20 according to IEC 60529
[Ui] rated insulation voltage	690 V according to IEC 60947-1
Connections - terminals	Connector 1 flexible AWG 4 Connector 1 solid AWG 4 Connector 1 cable(s) 1.5...10 mm ² flexible with Connector 1 cable(s) 1.5...16 mm ² flexible without Connector 1 cable(s) 1.5...25 mm ² solid Connector 2 cable(s) 1.5...2 mm ² flexible with Connector 2 cable(s) 1.5...6 mm ² solid Connector 2 cable(s) 2.5...4 mm ² flexible without Screw clamp terminals 1 flexible AWG 4 Screw clamp terminals 1 solid AWG 4 Screw clamp terminals 1 cable(s) 1.5...10 mm ² flexible with Screw clamp terminals 1 cable(s) 1.5...16 mm ² flexible without Screw clamp terminals 1 cable(s) 1.5...25 mm ² solid Screw clamp terminals 2 cable(s) 1.5...2 mm ² flexible with Screw clamp terminals 2 cable(s) 1.5...6 mm ² solid Screw clamp terminals 2 cable(s) 2.5...4 mm ² flexible without
Tightening torque	1.7 N.m - on screw clamp terminals 2.2 N.m - on connector
Product weight	0.04 kg

Environment

RoHS EUR status	Compliant
RoHS EUR conformity date	0601