

RT5MP

5-pole TINY chassis connector, nickel housing, gold plated contacts, max. panel thickness: 6 mm

| Product | |
|---------------------------|---------------------------|
| Gender | male |
| Electrical | |
| Contact resistance | < 5 mΩ |
| Dielectric strength | > 0.5 kVdc |
| Insulation resistance | > 1 GΩ |
| Rated current per contact | < 5 A |
| Mechanical | |
| Lifetime | > 1000 mating cycles |
| Wiring | Solder contacts |
| RW / Straight | no |
| Material | |
| Contact plating | Au |
| Contacts | Brass |
| Insert | PA 6.6 30 % GF |
| Shell | Zinc diecast |
| Shell plating | Black |
| Labeling | no |
| Environmental | |
| Solderability | Complies with IEC 68-2-20 |
| Temperature range | -30 °C to +80 °C |