

6.02109.50

BS 18 LTX Quick
4007430199225

18 Volt cordless drill / screwdriver BS 18 LTX Quick



0210900S_51.EPS

- Selectable impuls mode for precise driving of screws and comfortable drilling
- Variospeed (V) electronics for infinitely variable speed change
- Precision Stop: Torque coupling with precise electrical switch off to ensure extremely long lifetime for the tool
- Quick stop for rapid fastening of screws
- Metabo "Quick": Quick change of tool holder and tool being used, for example, changing from drilling mode to screwdriver mode in seconds
- Spindle with hexagon recess for screwdriver bits
- Neck (Ø 43 mm) for versatile use
- Integrated working light for good vision even in dark corners
- Die cast aluminium gear housing for optimum heat dissipation and stability
- Gear switch operable with one hand, suitable for right and left-handed users
- Multifunctional monitoring system to protect the machine and battery pack
- AIR COOLED technology for speedy charging and long service life
- Robust battery packs with capacity display for checking the charge status
- 3 year battery pack warranty

Scope of delivery

Quick change chuck, Quick change bit holder, Side handle, Tension ring with bit depot for 6 bits, 2 Li-Power Extreme battery packs (18 V/3.0 Ah), "AIR COOLED" quick charger ASC 30, Plastic carry case

Comparative technical values

Type of battery pack	Li-ion
Battery pack voltage	18 V
Capacity of battery pack	3,0 Ah
Maximum torque, soft	42 Nm
Pulse torque	46 Nm
Maximum torque, hard	96 Nm
Adjustable torque	1,5 - 13 Nm
- Drill diameter in	
- Steel	13 mm
- Wood	50 mm
Idle revolutions	0 - 400 / 0 - 1.400 /min
Chuck adapter	1,5 - 13 mm
Weight (including battery pack)	2 kg