

## Main

Range of product	Harmony XVR
Product or component type	Prewired rotating mirror beacon
Sound signalling	Without
Device short name	XVR
Mounting diameter	120 mm
IP degree of protection	IP23 conforming to IEC 60529
[Us] rated supply voltage	24 V AC/DC
Light source	High luminosity LED, red

## Complementary

Material	ABS (acrylonitrile butadiene-styrene) (body part) AS (globe)
CAD overall width	120 mm
CAD overall depth	120 mm
Product weight	0.5 kg
Marking	CE
Product mounting	By 3 M5 screws
Supply voltage limits	19...30 V DC 21.6...26.4 V AC
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	125 mA
Flashing frequency	2.3 Hz
Clamping connection capacity	0.83 mm <sup>2</sup>
AWG gauge	18
Cable length	400 mm

## Environment

Standards	EN 61000-6-2 EN 61000-6-4
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Class of protection against electric shock	Class II conforming to IEC 61140
RoHS EUR status	Compliant
RoHS EUR conformity date	0808

Rotating Mirror Beacon

Dimensions



