



## Main

Range of product	Harmony XVR Application
Product or component type	Rotating mirror beacon
Component name	XVR
Mounting diameter	165 mm
Light source	Orange bulb included
Bulb type	Halogen with H1 base
Power dissipation in W	70 W
[Us] rated supply voltage	24 V AC/DC

## Complementary

Material	Glass reinforced polyamide 6 on base unit Polycarbonate on domed lens unit
Clamping connection capacity	$\leq 1 \times 1.5 \text{ mm}^2$
Cable entry	1 tapped entry for cable gland (included), M20
[Ui] rated insulation voltage	250 V conforming to EN/IEC 60947-1
Current consumption	$< 3100 \text{ mA}$
[Uimp] rated impulse withstand voltage	4 kV conforming to EN/IEC 60947-1
Service life in hours	$> 2000 \text{ h}$
Operating position	Horizontal
Flashing frequency	3 Hz
CAD overall width	165 mm
CAD overall height	202 mm
CAD overall depth	165 mm
Product weight	1.165 kg

## Environment

Standards	CSA C22-2 No 14 EN/IEC 60947-1 EN/IEC 60947-5-1 UL 508
Protective treatment	TC
Ambient air temperature for storage	$-40 \dots 70 \text{ }^\circ\text{C}$
Ambient air temperature for operation	$-20 \dots 50 \text{ }^\circ\text{C}$
Class of protection against electric shock	Class I conforming to EN/IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
NEMA degree of protection	NEMA 4X (indoor) conforming to CSA 22 NEMA 4X (indoor) conforming to UL 508
RoHS EUR status	Will not be Compliant