


Snap Action, Standard




Features

- Actuator: Unidirectional Short Hinge Roller Lever



NTE Type No.	Circuitry	Max. Pre-Travel	Min. Over Travel	Max. Operating Force	Max. Differential	Diag No.
54-430	SPDT	0.09"	0.02"	170g	0.02"	S55

S55



Specifications

Current Rating: 15A 125/250/480VAC, 0.5A 125VDC, 0.25A 250VDC
1/8 HP 125VAC, 1/4 HP 250VA

Contact Resistance: 50 Milliohms (max.) initial

Insulation Resistance: 100 Megohms at 500VDC

Dielectric Strength: 1000VAC (50/60Hz for 1 minute)

Temperature Rating: -13° to +176°F (-25° to +80°C) with no icing

Electrical Life: 500,000 cycles min. (under rated load)

Mechanical Life: 20,000,000 cycles min.

Terminal Type: Screw Terminal

Snap Action, Standard




Features

- Actuator: Panel Mount Roller Plunger



NTE Type No.	Circuitry	Max. Pre-Travel	Min. Over Travel	Max. Operating Force	Max. Differential	Diag No.
54-438	SPDT	0.02"	0.22"	350g	0.002"	S56

S56



Specifications

Current Rating: 15A 125/250/480VAC, 0.5A 125VDC, 0.25A 250VDC
1/8 HP 125VAC, 1/4 HP 250VA

Contact Resistance: 50 Milliohms (max.) initial

Insulation Resistance: 100 Megohms at 500VDC

Dielectric Strength: 1000VAC (50/60Hz for 1 minute)

Temperature Rating: -13° to +176°F (-25° to +80°C) with no icing

Electrical Life: 500,000 cycles min. (under rated load)

Mechanical Life: 20,000,000 cycles min.

Terminal Type: Screw Terminal