

Aven Inc.
4595 Platt Rd.
Ann Arbor, MI 48108
Phone: 734.973.0099
Email: info@aventools.com • **Web Address:**www.aventools.com

Item # 26700-301, zipScope Wireless USB Microscope

\$149.00



zipScope Wireless USB Microscope

Our wireless zipScope lets you explore and capture digital images without any interference from wires hanging from the top of the microscope. Comes with a USB dongle that plugs into your PC and transmits to the rechargeable hand held microscope. Magnification range is 10-20x optical, 120x digital, giving you a wide range of viewing possibilities. Great for examining electronics, circuit boards, jewelry, small parts, quality control, or just learning or teaching.

[FEATURES](#) · [SPECIFICATIONS](#)

FEATURES

- Battery life: 2 hours under constant use
- Image & Video Capture software included
- Image format: Jpeg, BMP
- Magnification range 10x-120x optical, 200x digital
- Metal Stand included
- Rechargeable lithium ion battery, 3.7V
- Video format: AVI
- Wireless digital hand held microscope 0.3 mega pixel
- Wireless range: 10 meters

SPECIFICATIONS

| | |
|------------------|---------------------------------|
| Image Sensor | 1/2" Color CMOS |
| Image Resolution | 0.3M |
| Frame Rate | 15 fps |
| Magnification | 10x-20x optical 120x digital |
| Shutter Speed | 1 sec to 1/1000 sec |
| LED Light Type | 8 White LEDs |

| | |
|---------------|---|
| Exposure | Automatic |
| O/S | Windows XP, SP2 & Vista & 7 |
| White Balance | Automatic |
| Focus Range | Manual, 10mm to 500mm |
| Power Source | Dongle power supply 5V DC from USB port |
| Weight | 0.65 lb |
