

Manufacturer Part No: JF1R6-CR3-41

Length=100mm



#### Component Parts

Item No.	Item	Description	Part No.
1.	Cable Type	UMM-113_UFL Coaxial Cable	UMM-113_UFL
2.	Connector A	SMA Reverse Polarity Solder Bulkhead Jack (8mm Hex. Flange) Gold	MA02-0113-R01-8-R
3.	Connector B	UMM (UFL) Crimp Right Angle Plug Gold	UM17-0113-CD1
4.	Sleeving A	Heatshrink Sleeving Black	HSS-B-H1.1mm
5.	Sleeving B	Sleeving None	None-1mm
6.	Length & Reference	Tip to Tip – 100mm (+2mm/-0mm)	

#### Specifications

Item	Max. Frequency	Body Material	Dielectric	Impedance	Diameter	Attenuation/m
Cable Type	6 GHz	FEP	FEP	50 ohms	1.13mm	3dB @ 2.5GHz
Connector A	6 GHz	Brass	FEP	50 ohms	N/A	N/A
Connector B	6 GHz	Phosphor Bronze	PBT	50 ohms	N/A	N/A

#### Assembly Description

SMA Reverse Polarity Solder Bulkhead Jack (8mm Hex. Flange) Gold to UMM (UFL) Crimp Right Angle Plug Gold, UMM-113\_UFL, 100mm