

# T&B® Fittings



**T&B Catalog Number:** EFC150  
**UPC Number:** 78621078965  
**Description:** 1 1/2" Black Corrugated PVC flexible tubing. For use with Bullet™ Liquidtight Fittings.

**Status:** Active



### WEB\_USE

-T&B Product Line 012

### Features

- Maximum flexibility in tight applications.
- Extremely fast installation
- Liquidtight with specified fittings.
- Good tensile strength provides excellent pullout protection and smooth inner diameter allows easy wire pulling.

### General

- Material PVC
- Color Black
- Recommended industrial applications Protection of fiber optic cable, installation of instrumentation and control cable, indoor and outdoor lighting, packaging equipment, marine and ship-board wiring, and flexing-component wiring protection on robots, graphic arts equipments, etc.

### Dimension Information

- I.D. - Minimum (inches) 1.575
- I.D. - Maximum (inches) 1.600
- O.D. - Minimum (inches) 1.865
- O.D. - Maximum (inches) 1.900
- Conduit Size (inches) 1 1/2

### Packaging

- T&B Order Multiple 50
- Package in Units 50
- T&B Sold in UOM Feet
- T&B Weight Per UOM 36.8 lbs. per 100

### Application Support

- Guide to Nonmetallic Conduit Applications Available on Website
- XTRAFLEX System Specifications Available on Website

### Notes

- \*Note OEM Grade U.L. Recognized
- \*\*Note Broad operating temperature range - 18°F; C to +60°F; C (-2°F; F to +140°F; F)
- \*\*\*Note Flammability rating VW-1 (vertical wire) UL 224.

### Certifications

- RoHS Compliance Yes

### Certifications



File Nbr:  
E 96548

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)