

T&B® Fittings



T&B Catalog Number: LTC050
UPC Number: 78621078954
Description: 1/2" PVC Industrial Grade Type B smooth non-metallic liquidtight conduit; color-Black. For use with Bullet® Liquidtight Fittings.
Status: Active

WEB_USE

-T&B Product Line 012

Features

- Fast installation, even in tight or cramped spaces.
- Smooth inner diameter allows easy wire pulling.
- Smooth outer jacket uses material approved for outdoor use, is sunlight resistant and oil resistant.
- Lightweight and liquidtight.

Application

- UL Listed for direct burial

General

- Material PVC
- Color Black
- Recommended industrial applications Machine tools, motor hookups, food processing equipment, extensions from wire ways, and sensor and micro switch wiring found in control consoles.

Dimension Information

- I.D. - Minimum (inches) 0.622
- I.D. - Maximum (inches) 0.642
- O.D. - Minimum (inches) 0.820
- O.D. - Maximum (inches) 0.840
- Conduit Size (inches) 1/2

Packaging

- T&B Order Multiple 100
- Package in Units 100
- T&B Sold in UOM Feet
- T&B Weight Per UOM 13.13 lbs. per 100

Application Support

- Guide to Nonmetallic Conduit Applications Available on Website
- XTRAFLEX System Specifications Available on Website

Notes

- *Note XTRAFLEX® Type B Conduit, LTC series only, suitable for hazardous location where general purpose equipment is specifically permitted by the NEC Class I Div 2; Class II Div 1 & 2; Class III Div 1 & 2, NEC Article 501-4(b), 502-4(a)(b); and 503-3(a)(b).

Certifications

- RoHS Compliance Yes

Certifications



File Nbr:
E 95745

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com