




# Sta-Kon®

**T&B Catalog Number:** RA18-10F  
**UPC Number:** 78621080392  
**Description:** Insulated Nylon Fork Terminal For Wire Range 22-16 Stud Size #10, Red

**Status:** Active



### WEB\_USE

-T&B Product Line	029
-US Cutsheet PDF Catalog Link	<a href="http://www-public.tnb.com/contractor/docs/stakon.pdf">http://www-public.tnb.com/contractor/docs/stakon.pdf</a>

### Features

-	Inner bronze insulation grip sleeve lengthens flex radius of conductor and eliminates conductor creep. Nylon jacket is color-coded.
---	---

### General

-Insulation Type	Insulated Nylon
-Terminal Series	RA
-Material	Copper
-Finish	Electro -Tin Plated
-Color	Red
-Wire Range	22-16
-Stud Size	#10

### Dimension Information

-Maximum Insulation (inches)	.136
-Stock Thickness	.03
-A (inches)	.86
-B (inches)	.31
-C (inches)	.25
-M (inches)	.71

### Specifications

-Temperature Rating	105°C
-Voltage Rating	600V
-Flammability Rating	UL 94 V-2

### Tooling

-Tool Charts	Available on Website
-Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003, WT145A
-Recommended Tool	ERG4001

### Packaging

-T&B Order Multiple	100
-T&B Inner Pack	100
-Package in Units	500
-Package Type	Standard
-T&B Sold in UOM	Each
-T&B Weight Per UOM	0.25 lbs. per 100
-Alternate Package Qty	RA1153

### Application Support

-Overview	Available on Website
-Wire Guide Tables	Available on Website

### Certifications

-RoHS Compliance Yes

### Certifications



File Nbr:

E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com