



## Main

Range of product	Harmony XAP
Product or component type	Empty control station without hinges
Device short name	XAPA
Product destination	For Ø 30.5 mm control and signalling units
Product front plate size	85 x 146 mm
Usable depth	83 mm
Number of cut-out	4 cut-outs
Number of vertical rows	2
Colour of base of enclosure	Grey
Colour of cover	Grey
Material	Glass reinforced polyester
Product mounting	Flush mounting
IP degree of protection	IP65 conforming to IEC 60529 IP657 conforming to NF C 20-010
Resistance to chemical agents	High resistant to acids High resistant to all solvents High resistant to bases High resistant to diesel High resistant to mineral salts High resistant to oils and greases High resistant to petrol High resistant to sea water

## Complementary

Cable entry	Undrilled
Flame retardance	M3 conforming to CSTB VO conforming to UL 94
Product weight	0.47 kg

## Environment

Protective treatment	TC TH
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Class of protection against electric shock	Class II conforming to NF C 20-030 Class II conforming to IEC 60536
Fire resistance	850 °C conforming to NF C 20-455 960 °C conforming to IEC 92
RoHS EUR conformity date	0601
RoHS EUR status	Compliant