

# ADAM-4541

# ADAM-4542+

# ADAM-4561/4562

**Multi-mode Fiber Optic to RS-232/422/485 Converter**  
**Single-mode Fiber Optic to RS-232/422/485 Converter**  
**1-port Isolated USB to RS-232/422/485 Converter**



ADAM-4541



ADAM-4542+



ADAM-4561/4562



## Specifications

### General

- Power Input Unregulated 10 ~ 30 V<sub>DC</sub>
- Connectors 1 x plug-in terminal block (#14 ~ 22 AWG)  
(RS-232/422/485)  
2 x ST fiber connector
- Power Consumption 1.5 W @ 24 V<sub>DC</sub>

### Serial Communications

- Communication Mode Asynchronous
- Speed Modes (bps) 1,200, 2,400, 4,800, 9,600, 19.2 k, 38.4 k, 57.6 k, 115.2 k and RS-232/422 mode (switchable)
- Transmission Mode Full/half duplex, bidirectional

### Fiber Optic Communications

- Optical Power Budget (Attenuation) 12.5 dB (measured with 62.5/125 μm)
- Transmission Distance 2.5 km
- Transmission Mode Multi mode (Send and Receive)
- Wavelength 820 nm

## Specifications

### General

- Power Input Unregulated 10 ~ 30 V<sub>DC</sub>
- Connectors 1 x plug-in terminal block (#14 ~ 22 AWG)  
(RS-232/422/485)  
1 x SC fiber connector
- Power Consumption 3 W @ 24 V<sub>DC</sub>

### Serial Communications

- Communication Mode Asynchronous
- Speed Modes (bps) 1,200, 2,400, 4,800, 9,600, 19.2 k, 38.4 k, 57.6 k, 115.2 k and RS-232/422 mode (switchable)
- Transmission Modes Full/half duplex, bidirectional

### Fiber Optic Communications

- Optical Power Budget (Attenuation) 15 dB
- Transmission Distance 15 km
- Transmission Mode Single mode (Send and Receive)
- Wavelength 1310 nm

## Specifications

### General

- Connectors Network: USB-type A connector (type A to type B cable provided)  
Serial:  
ADAM-4561 1 x plug-in terminal (#14 ~ 22 AWG) (3-wire RS-232/422/485)  
ADAM-4562 1 x DB-9 serial connectors (9-wire RS-232)
- Isolation Voltage ADAM-4561: 3,000 V<sub>DC</sub>  
ADAM-4562: 2,500 V<sub>DC</sub>
- Power Consumption ADAM-4561: 1.5 W @ 5 V  
ADAM-4562: 1.1 W @ 5 V
- Driver Support Windows 98/2000/XP
- Full Compliance with USB v1.1 specifications

### Serial Communications

- Speed Modes (bps) 75 bps to 115.2 kbps
- Transmission Modes Full/half duplex, bidirectional

## Common Specifications

### Environment

- Humidity 5 ~ 95% RH
- Operating Temperature ADAM-4541/4542+: -10 ~ 70° C (14 ~ 158° F)  
ADAM-4561/4562: 0 ~ 70° C (32 ~ 158° F)
- Storage Temperature -25 ~ 85° C (-13 ~ 185° F)

## Ordering Information

- ADAM-4541 Multi-mode Fiber to RS-232/422/485 Converter
- ADAM-4542+ Single-mode Fiber to RS-232/422/485 Converter
- ADAM-4561 1-port Isolated USB to RS-232/422/485 Converter
- ADAM-4562 1-port Isolated USB to RS-232 Converter