

NYS323**NYS Product Range / DIN Connectors**

TECHNICAL DATA

Electrical

Rated Current: Depends on mating connector
Contact Resistance: Depends on mating connector
Insulation Resistance: > 1 G Ohm
Dielectric strength: 500 dc

Mechanical

Life Cycles: 5000
Cable OD: 4-9 mm
Solderability: IEC68-2-20
Operating Temperature: -25° C to +70° C

Material

Housing/Handle: Brass Ni/Au/black plated or Zinc Diecast
Insulation: Thermoplastic
Contacts: Brass Ni/Au plated
Strain Relief: CRIMP type SnCe plated

Copyright © 2005
Neutrik® AG.
All Rights Reserved.



NEUTRIK®
CONNECTING THE WORLD

Neutrik® AG - Headquarters

Im alten Riet 143
9494 Schaan
Principality of Liechtenstein
phone: +423 2372424
fax: +423 2325393
email: neutrik@neutrik.com
net: <http://www.neutrik.com>