

## General Purpose Labels

### General Pre-Cut Labels

Order Reference	Diagram	Labels per Roll	Material	Colour	Dimensions – mm	
					A	B
PTL-80-424	◇	250	B-424	White	19.05	22.86
PTL-20-424	▲	100	B-424	White	50.80	25.40
BPTL-20-424	▲	1000	B-424	White	50.80	25.40
PTL-22-424	▲	100	B-424	White	76.20	25.40
PTL-37-424	▲	100	B-424	White	76.20	48.26
PTL-38-424	▲	100	B-424	White	101.60	48.26
PTL-10-425	▲	750	B-425	White	19.05	6.35
PTL-10-8425	▲	750	B-425	White	19.05	6.35
PTL-105-427-AW	▲	750	B-427	White	27.94	6.35
PTL-30-427-AW	▲	250	B-427	White	38.10	19.05
PTL-78-427-AW	▲	250	B-427	White	48.26	25.40
PTL-7-432	▲	500	B-432	Clear	12.70	12.70
PTL-10-432	▲	750	B-432	Clear	19.05	6.35
PTL-11-432	▲	500	B-432	Clear	19.05	12.70
PTL-17-432	▲	500	B-432	Clear	25.40	12.70
PTL-16-435	▲	500	B-435	Silver	25.40	9.53
PTL-17-435	▲	500	B-435	Silver	25.40	12.70
PTL-19-435	▲	250	B-435	Silver	25.40	25.40
PTL-29-435	▲	500	B-435	Silver	38.10	12.70
PTL-30-435	▲	250	B-435	Silver	38.10	19.05
PTL-31-435	▲	250	B-435	Silver	38.10	25.40
PTL-32-435	▲	250	B-435	Silver	38.10	38.10
PTL-20-435	▲	100	B-435	Silver	50.80	25.40
PTL-37-435	▲	100	B-435	Silver	76.20	48.26
PTL-38-435	▲	100	B-435	Silver	101.60	48.26
PTL-17-449	▲	500	B-449	White	25.40	12.70
PTL-16-483	▲	500	B-483	White	25.40	9.53
PTL-17-483	▲	500	B-483	White	25.40	12.70
PTL-19-483	▲	250	B-483	White	25.40	25.40
PTL-65-483	▲	250	B-483	White	34.93	25.40
PTL-29-483	▲	500	B-483	White	38.10	12.70
PTL-30-483	▲	250	B-483	White	38.10	19.05
PTL-31-483	▲	250	B-483	White	38.10	25.40
PTL-32-483	▲	250	B-483	White	38.10	38.10
PTL-61-483	▲	100	B-483	White	50.80	12.70
PTL-20-483	▲	100	B-483	White	50.80	25.40
PTL-37-483	▲	100	B-483	White	76.20	48.26
PTL-62-483	▲	50	B-483	White	101.60	19.05
PTL-23-483	▲	100	B-483	White	101.60	25.40
PTL-63-483	▲	50	B-483	White	203.20	19.05
PTL-16-486	▲	500	B-486	Silver	25.40	9.53
PTL-17-486	▲	500	B-486	White	25.40	12.70
PTL-19-486	▲	250	B-486	Silver	25.40	25.40
PTL-29-486	▲	500	B-486	Silver	38.10	12.70
PTL-30-486	▲	250	B-486	Silver	38.10	19.05
PTL-31-486	▲	250	B-486	Silver	38.10	25.40
PTL-32-486	▲	250	B-486	Silver	38.10	38.10
PTL-20-486	▲	100	B-486	Silver	50.80	25.40
PTL-37-486	▲	100	B-486	Silver	76.20	48.26
PTL-38-483	▲	100	B-486	White	101.60	48.26
PTL-38-486	▲	100	B-486	Silver	101.60	48.26
PTL-16-489	▲	500	B-489	White	25.40	9.53
PTL-17-489	▲	500	B-489	White	25.40	12.70
PTL-19-489	▲	250	B-489	White	25.40	25.40
PTL-29-489	▲	500	B-489	White	38.10	12.70
PTL-30-489	▲	250	B-489	White	38.10	19.05
PTL-31-489	▲	250	B-489	White	38.10	25.40
PTL-32-489	▲	250	B-489	White	38.10	38.10
PTL-20-489	▲	100	B-489	White	50.80	25.40
PTL-37-489	▲	100	B-489	White	76.20	48.26
PTL-38-489	▲	100	B-489	White	101.60	48.26
PTL-112-490	▲	500	B-490	White	31.75	9.53
PTL-113-490	◇	100	B-490	White	38.10	55.88
PTL-114-490	◇	100	B-490	White	38.10	98.43
PTL-76-490	▲	250	B-490	White	41.28	15.24
PTL-78-490	▲	250	B-490	White	48.26	25.40
PTL-82-499	+	500	B-499	White	–	9.53 Diameter
PTL-82-499YL	+	500	B-499	Yellow	–	9.53 Diameter
PTL-83-499	+	500	B-499	White	–	12.70 Diameter
PTL-83-499YL	+	500	B-499	Yellow	–	12.70 Diameter
PTL-84-499	▲	500	B-499	White	22.86	12.70
PTL-81-499	▲	750	B-499	Yellow	48.26	6.35
PTL-78-499	▲	250	B-499	White	48.26	25.40

