

Main

Range of product	Harmony XAC
Product or component type	Head for pushbutton
Component name	XACB
Marking	Unmarked
Operator additional information	Booted
Operating travel	16 mm
Cap/Operator or lens colour	White
Product compatibility	XESD1181 XESD1191 XESD1281 XESD1291
Sale per indivisible quantity	10

Complementary

Product weight	0.005 kg
----------------	----------

Environment

Standards	CSA C22-2 No 14 EN 60947-5-1 IEC 60947-5-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	15 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	100 gn conforming to IEC 60068-2-27
Class of protection against electric shock	Class II conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 50102
RoHS EUR status	Compliant
RoHS EUR conformity date	0627