



- Power Supply: 220 V or 115 V
- Maximal Power: 75 W
- Temperature Range : 350 °F ~ 895°F / 175 °C ~ 480°C
- Length of Power Cord: 79 Inches / 2 Meters
- Temperature Stability: ±40 °F / ±5 °C
- Length of the Foot Pedal's Wire: 79 Inches / 2 Meters
- Motor Output: DC 12V , 3.42 W
- Fan Output: 4.5 W
- Solder Feed Time: 0 ~1 Second
- Solder Feed Speed: 0 ~ 4 Inches (0 ~ 100mm) / Second
- Controlling Mode: Pulse and Continuous (Optional)
- Usable Solder Dia.: 0.024 ~ 0.063 Inches / 0.6 ~ 1.6 mm
- Retract Feed Speed: 0 ~ 4 Inches (0 ~ 100mm) / Second
- Exterior Dimension(L x W x H): 14.5 x6.4 x 12.9 (Inches)
368 x 163 x 327(mm)
- Weight (Net): 6.8 Lbs. / 3.1 Kg
- Vertical Swing Adjustment: 15 °up and 45 ° down
- Height Adjustment: 7" to 10" while the unit's vertical range is at 90 ° from the base of the unit
- Horizontal Swing Adjustment: 54 ° from 0 ° position (total of 108 °)
- RoHS Compliant
- CE Approved