



BU-00000- *
Part # color

* 0 - Black 5 - Green
2 - Red 6 - Blue
4 - Yellow 9 - White

CLIPS & INSULATORS

BU-60TBO Threaded Barrel Alligator Clip - 10 Amp



- Steel, standard Alligator clip with steel threaded barrel
- Connection to any 8-32 male test prod or screw
- Nose width 0.13"

BU-60H Alligator Clip with Insulated Acetate Handle 10 Amp

- Stainless steel body, rivet, and spring
- Jaw opens 5/16" (7.9mm)
- Available in black, red, yellow, green, blue and white
- Nose width 0.13"



Alligator Clip with Acetate Handle & Screw - 10 Amp BU-60HS-* (Steel) BU-60CHS-* (Solid Copper)

- Available in black, red, yellow, green, blue and white
- Nose width 0.13"
- Federal Spec.: Type TCI-1(red), TCI-2 (Black), W-C-440B (BU-60CHS-*)

BU-61 Alligator Clip with Gold Plated Beryllium Copper Cage Spring Barrel

- Nickel-plated Steel clip and brass insert
- Cage spring accepts standard (0.080dia.) prod needle
- Nose width 0.13"
- Jaw opens 5/16" (7.9mm) max.



©2003 Mueller Electric Company. All rights reserved.
Problems with the site should be reported to the [webmaster](#).