




**Panel Mount Indicator, Non-Relampable
Neon and Incandescent Technology
Mounting Hole, Ø 0.310"**



All dimensions are in inches



Minimum panel thickness: 0.030"

6" leads with 1/2" strip are standard

Storage temperature T_{STG} : -25°C - +80°C
Ambient temperature T_A : -20°C - +60°C
Voltage tolerance V_{OP} : ±10%

Part No.	Lens Color	Voltage	Current mA	Rated Life
Neon 115VAC Series				
WL-2150A1	Red	105-125VAC	1.5mA	25,000 Hrs
WL-2150A2	Clear	105-125VAC	1.5mA	25,000 Hrs
WL-2150A3	Amber	105-125VAC	1.5mA	25,000 Hrs
WL-2150A4	White	105-125VAC	1.5mA	25,000 Hrs
WL-2152A5	Green	105-125VAC	1.5mA	25,000 Hrs
WL-2152A6	Blue	105-125VAC	1.5mA	25,000 Hrs
Neon 230VAC Series				
WL-2151A1	Red	208-250VAC	1.5mA	25,000 Hrs
WL-2151A2	Clear	208-250VAC	1.5mA	25,000 Hrs
WL-2151A3	Amber	208-250VAC	1.5mA	25,000 Hrs
WL-2151A4	White	208-250VAC	1.5mA	25,000 Hrs
WL-2153A5	Green	208-250VAC	1.5mA	25,000 Hrs
WL-2153A6	Blue	208-250VAC	1.5mA	25,000 Hrs
Incandescent 12V Series				
WL-2194A1-12V	Red	12V-14V	80mA	25,000 Hrs
WL-2194A3-12V	Amber	12V-14V	80mA	25,000 Hrs
WL-2194A4-12V	White	12V-14V	80mA	25,000 Hrs
WL-2194A5-12V	Green	12V-14V	80mA	25,000 Hrs
Incandescent 28V Series				
WL-2194A1-28V	Red	24V-28V	40mA	25,000 Hrs
WL-2194A3-28V	Amber	24V-28V	40mA	25,000 Hrs
WL-2194A4-28V	White	24V-28V	40mA	25,000 Hrs
WL-2194A5-28V	Green	24V-28V	40mA	25,000 Hrs

Body Material: Nylon, white
Lens Material: Polycarbonate
Bezel Finish: Chrome
Wire Gauge: 18 AWG
Wire Strip: 1/2"

Certifications: Most Wamco indicators carry Agency approvals. Please contact Wamco for the latest Agency information regarding the specific product series and voltage required.
Options: Additional options and lens styles available. Please contact Wamco for more information.

Drawn	SC	03/01/10	Panel Mount Indicators Neon and Incandescent	Datasheet: WL-215XAX Series WL-2194AX-XXX Series	Rev: 1
Checked	EB	03/01/10			
Approved	EB	03/02/10			