



### A compact high pressure washer with 130 bar

The C 130.1 is a domestic pressure washer which offers good performance level, a high level of comfort, flexibility and user-friendliness. This is for all types of low to medium frequency cleaning tasks around the house.

### PRODUCT FACTS

- Reliable aluminium pump.
- Trolley for high mobility.
- Storage of gun, nozzle and foam sprayer.
- Integrated storage for hose and electric cable.
- Pressure regulation.
- Click&Clean nozzle system ensures quick and easy change of nozzle.
- Automatic start/stop.
- Sturdy and robust design.
- Noise reduction by rubber suspension of motor pump unit.
- Interactive CD included in the machine packaging.

# Nilfisk

Nilfisk-ALTO UK  
 Gilwilly Industrial Estate Penrith, Cumbria CA 11 9BQ  
 Tel: +44 (0)1 768 86 89 95 - Fax: +44 (0)1 768 86 47 13  
[www.nilfisk-alto.co.uk](http://www.nilfisk-alto.co.uk)

United Kingdom

Print created: 20-03-2012 12:22  
 1 / 4

Prices subject to change without prior notice

Model	C 130.1-6 X-TRA
Ref. no	128470256
Description	C130.1-6 XTRA UK

**PRODUCT FEATURES**

AUTOMATIC START/STOP	■
CABLE STORAGE	■
TROLLEY	■
PRESSURE REGULATION	■
CLICK & CLEAN (C&C) NOZZLE CONCEPT	■
ALUMINIUM PUMP	■
GUN WITH QUICK CONNECTION AND SWIVEL	■
LANCE AND SPRAY GUN STORAGE	■
STORAGE OF ACCESSORIES	■

**Incl. accessories**





6520844 CLEANING TOOL	■
6411132 CLICK & CLEAN FOAM SPRAYE	■
126481132 G3 GUN WITH INTERMEDIATE	■
126481134 G3 LANCE COMPLETE	■
126481138 HOSE 6M	■
126481115 POWERSPEED	■
126481120 PR TORNADO DARK	■

**Technical specifications**

C130.1-6 XTRA UK

CABLE LENGTH (M)	5
VOLTAGE (V)	230
RATED POWER (KW)	1.7
POWER CONSUMPTION (A)	7.4
WATER FLOW QMAX/QIEC (L/H)	440/380
PUMP PRESSURE (BAR/MPA)	Max. 130/13
HOSE LENGTH (M)	6
MAX INLET TEMPERATURE (°C)	40
DIMENSIONS LXWXH (MM)	305x295x885
WEIGHT (KG)	15.8

Accessories		Ref. no	Min. required	C 130.1-6 X-TRA
	<b>Consumer nozzles</b>			
	POWERSPEED GREEN	126481115	1	■
	UNDERCHASSIS NOZZLE	6411135	1	■
	AUTO NOZZLE	6411136	1	■
	<b>Consumer Patio Plus</b>			
	PATIO CLEANER PLUS ACC	126411376	1	■
	<b>Consumer extension hose</b>			
	7M HP HOSE EXCELLENT	106411346	1	■
	HOSE 6M	126481138	1	■
	EXTENSION HOSE 7M	6410760	1	■
	<b>Consumer brushes</b>			
	GARDEN BRUSH	106411325	1	■
	RIM BRUSH	106411326	1	■
	HEAD FOR GARDEN BRUSH	106411327	1	■
	HEAD FOR RIM BRUSH	106411328	1	■
	ROTARY BRUSH	126411395	1	■
	ROTARY BRUSH	6410762	1	■
	AUTO BRUSH	6410765	1	■
AUTO BRUSH WITH SQUEEGEE	6411131	1	■	
	<b>Click &amp; Clean car kit</b>			
	CAR C C KIT BOX	128500086	1	■
	<b>Click &amp; Clean PAD kit</b>			
	PAD BOX ACC.	128500069	1	■
	<b>Consumer pressure washer acc.</b>			
	WATER FILTER	106411231	1	■
	WATER SUCTION SET	106411232	1	■

Accessories	Ref. no	Min. required	C 130.1-6 X-TRA	
<b>Consumer pressure washer acc.</b>				
	WALL HOOK	106411386	1	■
	WATER SUCTION KIT	126411387	1	■
	PR TORNADO DARK BLUE	126481120	1	■
	G3 GUN WITH INTERMEDIATE TUBE	126481132	1	■
	G3 LANCE COMPLETE	126481134	1	■
	ROOF CLEANER	128470040	1	■
	UNDERCHASSIS WASH LANCE	6410763	1	■
	VSB 120-1 (GREEN)	6410891	1	■
	CLICK & CLEAN FOAM SPRAYER	6411132	1	■
	AUTO KIT CLICK & CLEAN	6411134	1	■
	CLEANING TOOL	6520844	1	■
<b>More accessories</b>				
	Long fixed brush	126411795	1	■
	DRAIN/TUBE CLEANER 15M	6410766	1	■
	MULTI ANGLE ADAPTOR	6411138	1	■
<b>Consumer detergents</b>				
	ROOFCLEANER DETERGENT	128470041	1	■
	CAR COMBI CLEANER BOX 4X2.5 LTR	308000095	1	■
	METAL CLEANER BOX 4 X 2.5 LTR	308000096	1	■
	PLASTIC CLEANER BOX 4X 2.5 LTR	308000097	1	■
	STONE & WOOD CLEANER BOX 4X2.5	308000098	1	■
<b>Consumer BA valve</b>				
	NILFISK BA VALVE COMPLETE	106411177	1	■