

SVGA Monitor Extension Cables



- High quality, low loss moulded cable assemblies ideal for use as extensions or with switch boxes
- UL style 2919 cable - 3 core 75Ω coax (for primary, Red, Green and Blue) and 4x 26AWG twisted pair
- Low voltage, foil and braid screen cable with gold contacts

382737

Male/Female	Order Code	Price Each
0.5m	838-3308	
1m	838-3316	
2m	838-3324	
3m	838-3332	
5m	838-3340	
8m	838-3359	
10m	838-3367	
15m	838-3375	
20m	838-3383	
Male/Male		
1m	838-3405	
2m	838-3413	
3m	838-3421	
5m	838-3430	
8m	838-3448	
10m	838-3456	
15m	838-3464	
20m	838-3472	