



by Schneider Electric

List Price \$1,809.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Approvals	UL Listed - CSA Certified
Circuit Breaker Type	Standard
Features	VISI-TRIP trip indication
Ampere Rating	125A
For Use With	NQ & NQOD Panelboards/Interiors
General Application	Provides overload and short circuit protection
Type	QOB
Number of Poles	3-Pole
Wire Size	#4 to 300 AWG/kcmil(Al/Cu)
Phase	3-Phase
Marketing Trade Name	QO
Short Circuit Current Rating	22kA
Height	3.50 Inches
Voltage Rating	240VAC
Width	2.25 Inches
Space Required	6
Depth	2.91 Inches
Mounting Type	Bolt-On
Terminal Type	Box Lugs

Notes:

UL Listed for use ahead of QO, QO-GFI, QO-EPD, QOT, AND QO-PL 10kA circuit breakers to permit their application at 22kA fault level.

Shipping and Ordering

Category	00015 - Circuit Breakers, 1 Pole: 10 - 70 Amp, 2 Pole: 10 - 125 Amp, 3 Pole: 10 -160 Amp, Type QO
Discount Schedule	DE2
GTIN	00785901065470
Package Quantity	1
Weight	3.97 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	US

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.