



STARTER PKZ2

Part no.

**PKZ2/
S(110V50HZ,120V60HZ)**

Article no.

063570

Program

Rated uninterrupted current	I_u	A	40
-----------------------------	-------	---	----

Approbationen

UL approval	Yes
CSA approval	Yes
Product Standards	UL 508; CSA-C22.2 No. 14; IEC60947-4-1; CE marking
UL File No.	E36332
UL CCN	NLRV
CSA File No.	12528
CSA Class No.	3211-05
NA Certification	UL listed, CSA certified
Specially designed for NA	No

Technical data according to ETIM 4.0

Rated operation power at AC-3, 400 V		kWh	20
With integrated auxiliary switch			No
Rated permanent current I_u		A	40
With integrated under voltage release			No
Number of poles			3
Degree of protection (IP)			IP00
Connection type main current circuit			Screw connection

Characteristics

Cha_pkz2_G.pdf; Operating frequency

Additional product information (links)

AWA1280-0876 Motor-protective circuit-breaker	ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/08760303.pdf
AWB1210-1485 PKZ2 motor-protective circuit-breakers, overload monitoring of Ex e motors	ftp://ftp.moeller.net/DOCUMENTATION/AWB_MANUALS/h1485dgb.pdf
Motor starters and "Special Purpose Ratings" for the North American market	http://www.moeller.net/binary/ver_techpapers/ver953en.pdf
Busbar Component Adapters for modern Industrial control panels	http://www.moeller.net/binary/ver_techpapers/ver960en.pdf
PKZ 2 System - For Optimum Motor and System Protection	http://www.moeller.net/binary/ver_techpapers/ver952en.pdf