

Harting

Han 3 A 3 + $\frac{1}{2}$	Screw Terminal		Gland	Top Entry Hood	Gland	Panel Mount Housing	Panel Mount Housing	Surface Mount Housing	Gland	Cable to Cable	Gland	Gland
	Working Voltage	250V										
	Working Current	10A										
	Wire Gauge	2,5mm										
		(M) 09 20 003 2611	20mm	19 20 003 1440	20mm	09 20 003 0301	19 20 003 1250	20mm	19 20 003 1750	20mm	A20	
		(F) 09 20 003 2711										

Han 6 E 6 + $\frac{1}{2}$	Screw Terminal		Gland	Top Entry Hood	Gland	Panel Mount Housing	Panel Mount Housing	Surface Mount Housing	Gland	Two Side-Entry	Gland	Gland
	Working Voltage	380V										
	Working Current	16A										
	Wire Gauge	2,5mm										
		(M) 09 33 006 2601	20mm	L 19 30 006 1440	20mm	09 30 006 0301	19 30 006 1250	20mm	19 30 006 1290	2x20mm	A20	
		(F) 09 33 006 2701	25mm	H 19 30 006 0446	25mm	with thermoplastic cover 09 30 006 0302	with thermoplastic cover 19 30 006 1255		with thermoplastic cover 19 30 006 1295	2x20mm	A20	
			32mm	H 19 30 006 0447	32mm							

Han 10 E 10 + $\frac{1}{2}$	Screw Terminal		Gland	Top Entry Hood	Gland	Panel Mount Housing	Panel Mount Housing	Surface Mount Housing	Gland	Two Side-Entry	Gland	Gland
	Working Voltage	380V										
	Working Current	16A										
	Wire Gauge	2,5mm										
		(M) 09 33 010 2601	20mm	L 19 30 010 1440	20mm	09 30 010 0305	19 30 010 1250	20mm	19 30 010 1290	2x20mm	A20	
		(F) 09 33 010 2701	25mm	H 19 30 010 1441	25mm	with thermoplastic cover 09 30 010 0303			with thermoplastic cover 19 30 010 1295	2x20mm	A20	
			32mm	H 19 30 010 0547	32mm							

L = Low Construction H = High Construction

Harting

Han 10 E 16 + $\frac{\pm}{\pm}$	Screw Terminal			Side Entry Hood	Gland	Top Entry Hood	Gland	Panel Mount Housing	Surface Mount Housing	Two Side-Entry	Gland	Gland
	Working Voltage	380V			2 levers on the Housing		2 levers on the Housing		2 levers on the Housing	2 levers on the Housing		
	Working Current	16A										
	Wire Gauge	2,5mm										
				L 19 30 010 1520	20mm	L 19 30 010 1420	20mm	09 30 010 0301	L 19 30 010 1230	L 19 30 010 1270	A20	
				H 19 30 010 1521	25mm	H 19 30 010 1421	25mm		L 19 30 010 1231	L 19 30 010 0271	A22	
				H 19 30 010 0527	32mm	H 19 30 010 0427	32mm		H 19 30 010 0231	L 19 30 010 0272	A23	

Han 16 E 16 + $\frac{\pm}{\pm}$	Screw Terminal			Side Entry Hood	Gland	Top Entry Hood	Gland	Panel Mount Housing	Surface Mount Housing	Two Side-Entry	Gland	Gland
	Working Voltage	380V			1 lever on the Housing		1 lever on the Housing		1 lever on the Housing	1 lever on the Housing		
	Working Current	16A										
	Wire Gauge	2,5mm										
				L 19 30 016 1541	25mm	L 19 30 016 1441	25mm	09 30 016 0307	19 30 016 1251	19 30 016 1291	2x25mm	A22
				H 19 30 016 0547	32mm	H 19 30 016 1442	32mm	with thermoplastic cover 09 30 016 0306	with thermoplastic cover 19 30 016 1256	with thermoplastic cover 19 30 016 1296	2x25mm	A22
						H 19 30 016 0447	32mm					

L = Low Construction H = High Construction