

Products

- Products Overview
- [Product Search](#)
- Evaluate
  - FAQs
- Design a Solution
  - Part Drawings
  - PDF-Epoxy Applie
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor
- Install & Maintain
  - Installation Instructions
  - PDF-EMA Epoxy Ad ..

Home > Products Overview > Product Search >

Current refinements (click to remove) Search Tips

Part Number > EMS-A-D0

Your search criteria matched only one product, shown below

EMS-A-D0



These mounts are designed for application with Panduit EMA epoxy. Especially construction and maintenance applications where they eliminate the need to drill

- Provide a fast, strong, economical method to secure wire/cable to steel, alumin wood and most other surfaces
- Eliminate the need to drill holes

▪ Part Number	EMS-A-D0
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Epoxy Applied Cable Tie Mount
▪ Product Type	Cable Tie Mounts - Epoxy Applied
▪ Material	Weather Resistant Nylon 6.6
▪ Color	Black
▪ Height (In.)	0.26
▪ Height (mm)	6.6
▪ Length (In.)	0.98
▪ Length (mm)	24.9
▪ Width (In.)	1.00
▪ Width (mm)	24.9
▪ Adhesive Type	EMA Epoxy
▪ CE Compliant	No
▪ Environment	Outdoor
▪ Max. Bundle Diameter (mm)	4.8
▪ Max. Static Load (g)	4540
▪ Max. Static Load (Lbs.)	10.00
▪ Mounting Method	EMA epoxy
▪ Pricing Description	Cable Tie Mount, Epoxy Applied, WRBL
▪ Type	Tie Mount - User Supplied Adhesive
▪ Used With Cable Ties	M, I, S
▪ Min. Order UOM	PC
▪ Min. Order Qty.	500
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.