

1

2

3

4

5

CHARACTERISTICS:

MATERIAL:

COLOR: BLACK

OPERATING TEMPERATURE: -20°C UP TO 80°C

COMPLIANCE: LEAD FREE AND ROHS


PACKAGING:

10PCS/BAG

WIRE DIMENSION:

AWG: 16

Terminal A



3mm Pre-stripped

Terminal B


Wire Length 150mm*

Terminal A	649 008 137 22
Terminal B	Pre-stripped

RoHS Compliant

* Note: Wire UL 1007

PROJECTION:



GENERAL TOLERANCE

.X = +/- 0.2

.XX = +/- 0.15



APPROVAL: RJ

UNIT: MM

SCALE:

SHEET: 1/2

DRAW: QL

DESCRIPTION: WR-MPC4 FEMALE PRE-CRIMPED CONTACT

WERI PART NO: 649 800 116 015

SIZE

A4

G							
F							
E							
D							
C							
B							
A	18-OCT-11	PDF	GG				
REV	DATE	FILE	BY				

1

2

3

4

5

A

B

C

D

Note:
 1.Dimension
 Carton Size:40*30*20(CM)
 2.Quantity: 5000 Pcs/Carton



RoHS Compliant

G			
F			
E			
D			
C			
B			
A			
REV	DATE	FILE	BY

PROJECTION:


GENERAL TOLERANCE
 .X = +/- 0.2
 .XX = +/- 0.15



APPROVAL: RJ

UNIT: MM
 SCALE:
 SHEET: 2/2
 DRAW: QL

DESCRIPTION: WR-MPC4 FEMALE PRE-CRIMPED CONTACT
 WERI PART NO: 649 800 116 015

SIZE
A4